
Backbone[™] Media Platform Price List ■

March 28, 2012 Updated January 2, 2017 800-424-2432





Cutout Details



Enclosure

Enclosure shall consist of 3/4" thick 45# particle board with exposed surfaces finished with a minimum of .030" thick high pressure laminate. Access to internal wiring shall be provided by a lockable removable door with minimum dimensions measuring 10" tall by 48" long. Ventilation is provided through openings on each end measuring a minimum 8" x 15" and covered with powder coated perforated steel panels.

The Stationary units will be supported by

The Stationary units will be supported by two 11-gauge formed and welded steel supports containing leveling glides. These powder coated supports are bolted to the lower support cross members. This unit will be topped by a 1-1/8" thick 45# particle board top.

The Mobile units will be supported by four 2.44" diameter casters and contain rare earth ganging magnets on two sides. These unit will be topped with a 3/4" thick 45# particle board top. Mobile tables are available with three different base styles, (Enlite, Synthesis &Trek). Table tops are

either 3/4" or 1-1/8" thick 45# particle board topped with a minimum .030" HPL and backed with .020" HPL backer. All Mobile Tables will have (8) rare earth magnets to provide ganging options. Tables gang to the enclosure and each other in three different configurations.

All tops will be finished with a minimum .030" thick high pressure laminate and banded with 2mm polypropylene edge material and routered for the quantity and size of the chosen switching hardware.

Monitor Support

Monitor support shall consist of 3/4" thick 45# particle board with exposed surfaces finished with a minimum of .030" thick high pressure laminate. Units have T-nuts to attach to both Stationary and Mobile units with (6) bolts. For use with Backbone® tables only.



Cutout Patterns for Mobile Units

Size 23"W x 52"L	EXTRON (EX4)	EXTRON (EX5)	EXTRON (EX6)	EXTRON (EX7)	EXTRON (EX8)	FSR (FS1)	FSR (FS2)
25"W x 64"L							
27"W x 76"L							

Backbone® General Information

Cutout Patterns for Stationary Units (Page 1 of 2)

Unit Size	EXTRON 4 (EX4) CABLE CUBBY 202	EXTRON 5 (EX5) CABLE CUBBY 500	EXTRON 6 (EX6) CABLE CUBBY 700	EXTRON 7 (EX7) CABLE CUBBY 1200	EXTRON 8 (EX8) CABLE CUBBY 1400
64"W x 73"L					
66"W x 85"L					
68"W x 97"L					



Cutout Patterns for Stationary Units (Page 2 of 2)

Unit Size	FSR (FS1) T3 TABLE BOXES	FSR 2 (FS2) T6 TABLE BOXES
64"W x 73"L	O O O	0
66"W x 85"L	O O O O O O O	0
68"W x 97"L	O O O O O O	

Backbone® Stationary Unit

		MBER							
								Foot	
			Basic	Edge	Edge	Surface	Base	End Panel	Media
	MODEL	OVERALL SIZE	Model	Style	Color	Finish	Laminate	Color	Cutout
	Backbone® - Stationary Unit	64"W x 73"L x 29"H	BBNST73						
beess	All laminate table and base	66"W x 85"L x 29"H	BBNST85						
	 Media sharing equipment must be purchased separately 	68"W x 97"L x 29"H	BBNST97						
******	Reference diagram for Extron and FSR								
	grommet locations								
	End panel color is also used for the base feet								
	Support legs match WorkUp® table								
BNS	• 29" high surface								
	Back and a Charles and Hair Cafe Hairk	64"W x 73"L x 42"H	BBNSTC73						
Bedada	Backbone® - Stationary Unit - Cafe Height	66"W x 85"L x 42"H	BBNSTC85						
\sim	All laminate table and base	68"W x 97"L x 42"H	BBNSTC97						
STATE OF THE PARTY	 Media sharing equipment must be purchased separately 								
	Reference diagram for Extron and FSR								
	grommet locations								
	End panel color is also used for the base								
BBNS	feet • Support legs match WorkUp® table								
	• 42" high surface								
	'								
	Backbone - Master Key for Lock Core		31.13.0445						
HRDPT	 Allows access to all Backbone® panels 								
	with a single key								
			A	B	0	0	•	(a)	О
			w	U	G	U	G	U	U

HOW TO ORDER

Indicate the following information on order form:

- Quantity of each item.
 Model number, including options. See "How To Build a Model Number".
- 3. Any special service required.

Note: \bullet The \square indicates that a choice is required.

- \bullet The absence of the \square indicates that no choice is required.
- · Alpha-numeric characters in place of \square indicate that no other alternatives are available.

HOW TO BUILD A MODEL NUMBER

A Select basic model.

Select edge style.

74P - 74P edge

KN - Knife edge

Select edge color.

Refer to color addendum at ki.com or KI Fabrics & Finishes binder. Edge color offerings are based on edge

style selections.

DSelect top laminate.

Refer to color addendum at ki.com or KI Fabrics & Finishes binder.

Select base laminate.

Refer to color addendum at ki.com or KI Fabrics & Finishes binder.

Select foot/end panel finish. Refer to color addendum at ki.com or KI Fabrics & Finishes binder.

Select media cutout. - No cut-out EX4 - Extron 4 - Extron 5 EX6 - Extron 6

- Extron 7 EX7 EX8 - Extron 8 FS1 - FSR (T3) - FSR (T6)

INFORMATION

Grommet Cutouts by Table Size

Base Length Number of Grommet Cutouts

48" 4 6 72" 6





					<u></u>
Approx.					
Approx. Package Weight	d [Delivered	74P Edge	e Kni	ife Edge
		Pricing	(74P)	(KN	
236.0	¥ \$	5909	\$ 5676	\$	5909
279.0	#	5832	5832		6066
325.0	¥	6703	6450		6703
236.0	¥ \$	6719	\$ 6719	\$	6953
279.0	¥	6907	6907		7141
325.0	#	7591	7591		7843
1.07	¥ \$	5	N/A		N/A

SPECIAL SERVICES

Special Carton Marking

With specially marked information

N/C

Shipping Shipped k.d. freight prepaid f.o.b. Bonduel, Wisconsin 54107 factory. Freight class #85.

Specifications and prices are subject to change without prior notice.

Backbone® Stationary Unit with Radius Corners

			MODEL NU	MBER					
			Desir	Edua	Edua	Ourford	Descri	Foot	B.O. dia
	MODEL	OVERALL SIZE	Basic Model	Edge Style	Edge Color	Surface Finish	Base Laminate	End Panel Color	Media Cutout
	Backbone® - Stationary Unit with Radius	64"W x 73"L x 29"H	BBNSTR73						
tithicae	Corners	66"W x 85"L x 29"H	BBNSTR85						
	All laminate table and baseMedia sharing equipment must be	68"W x 97"L x 29"H	BBNSTR97						
******	purchased separately								
	 Reference diagram for Extron and FSR 								
	grommet locations • End panel color is also used for the base								
	feet								
BBNS	 Support legs match WorkUp® table 								
	29" high surface								
9	Backbone® - Stationary Unit with Radius Corners - Cafe Height • All laminate table and base • Media sharing equipment must be	64"W x 73"L x 42"H	BBNSTRC73						
		66"W x 85"L x 42"H	BBNSTRC85						
		68"W x 97"L x 42"H	BBNSTRC97						
*****	purchased separately								
	Reference diagram for Extron and FSR								
	grommet locations • End panel color is also used for the base								
DDNO	feet								
BBNS	Support legs match WorkUp® table 40" bigb curfees								
	 42" high surface 								
	Backbone - Master Key for Lock Core		31.13.0445						
HRDPT	Allows access to all Backbone® panels		01.10.0440						
TITIOT I	with a single key								
			A	B	Θ	0	•	G	Э

HOW TO ORDER

Indicate the following information on order form:

- 1. Quantity of each item.
- 2. Model number, including options. See "How To Build a Model Number".
- 3. Any special service required.

Note: \bullet The \square indicates that a choice is required.

- \bullet The absence of the \square indicates that no choice is required.
- · Alpha-numeric characters in place of \square indicate that no other alternatives are available.

HOW TO BUILD A MODEL NUMBER

A Select basic model.

Select edge style.

74P - 74P edge

KN - Knife edge

Select edge color.

Refer to color addendum at ki.com or KI Fabrics & Finishes binder.

Edge color offerings are based on edge style selections.

DSelect top laminate.

Refer to color addendum at ki.com or KI Fabrics & Finishes binder.

Select base laminate.

Refer to color addendum at ki.com or KI Fabrics & Finishes binder.

Select foot/end panel finish. Refer to color addendum at ki.com or KI Fabrics & Finishes binder.

Select media cutout. - No cut-out EX4 - Extron 4 - Extron 5 EX6 - Extron 6 EX7 - Extron 7 EX8 - Extron 8 FS1 - FSR (T3) - FSR (T6)

INFORMATION

Grommet Cutouts by Table Size

Base Length Number of Grommet Cutouts

48" 4 6 72" 6



Backbone® Stationary Unit with Radius Corners

•				
Approx. Packaged Weight	Delivered Pricing	74P Edge (74P)	Knife Edge (KN)	
236.0#	\$ 5676	\$ 5676	\$ 5909	
279.0#	5832	5832	6066	
325.0#	6450	6450	6703	
	\$ 6719	\$ 6719	\$ 6953	
279.0#	6907	6907	7141	
325.0#	7591	7591	7843	
1.0#	\$ 5	N/A	N/A	

SPECIAL SERVICES

Special Carton Marking

With specially marked information

N/C

Shipping Shipped k.d. freight prepaid f.o.b. Bonduel, Wisconsin 54107 factory. Freight class #85.

Specifications and prices are subject to change without prior notice.

Backbone® Mobile Unit

Includes three tables to dock against the center spine with magnets BBNMT76 has two 48" and one 60" table BBNMT88 has three 60" tables BBNMT88 has three 60" tables BBNMT100 has two 72" and one 60" table Media sharing equipment must be purchased separately Reference cutout diagram for Extron and FSR grommet locations Tables gang to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enitie® base Tables have a 5% angle on the short ends			MODEL NUMBER										
Pow x 88"x x 29"H 72"W x 100"L x 29"H BBNMT100 74P BBNMT100 BBNM BBNMT6 bright and the content of the content o			Model	Style	Option	Color	Finish	Table Leg Color			Laminate		
BNM Sackbone® - Mobile Unit Includes three tables to dock against the center spine with magnets BBMMT6 has two 48° and one 60° table BBMMT8 has three 60° tables BBMMT100 has two 72° and one 60° table BBMMT8 has three 60° tables BBMMT100 has two 72° and one 60° table Media sharing equipment must be purchased separately Reference cutout diagram for Extron and FSR gromment locations Tables gang to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enitle® base Tables have a 5% angle on the short ends Enitle® and Trek® casters come standard - 2 locking and 2 non-locking per table Synthesis® comes standard vith emedded casters on one end of		68"W x 76"L x 29"H	BBNMT76	74P									
BNM Jackbone® - Mobile Unit Includes three tables to dock against the center spine with magnets BBMMT76 has two 48° and one 60° table BBMMT76 has two 72° and one 60° table BBMMT80 has three 60° tables BBMMT100 has two 72° and one 60° table BBMMT90 has two 60° table BBMT90 has tw	ODD O	70"W x 88"L x 29"H	BBNMT88	74P									
Includes three tables to dock against the center spine with magnets BBMMT76 has two 48° and one 60° table BBMMT86 has three 60° tables BBMMT88 has three 60° tables BBMMT80 has two 72° and one 60° table BBMMT8100 has two 72° and one 60° table BBMMT8100 has two 72° and one 60° table BBMMT8100 has two 72° and one 60° table BBMMT80 has three 60° tables BBMMT80 has two 72° and one 60° table BBMMT80 has two 72° and one 60° table BBMMT80 has two 72° and one 60° table BBMMT80 has three 60° tables BBMT80 has three 60° tables BB		72"W x 100"L x 29"H	BBNMT100	74P									
Includes three tables to dock against the center spine with magnets BBMMT76 has two 48° and one 60° table BBMMT86 has three 60° tables BBMMT88 has three 60° tables BBNMT100 has two 72° and one 60° table BBMMT80 has two 72° and one 60° table BBMMT80 has two 72° and one 60° table BBMMT80 has two 72° and one 60° table BBMMT90 has two 72° and 60° table BBMMT90 has two 72° and 60° table BBMT90 has two 72° and 60° table BBMMT90 has two 72° and 60° tabl													
Includes three tables to dock against the center spine with magnets BBMMT76 has two 48° and one 60° table BBMMT86 has three 60° tables BBMMT88 has three 60° tables BBNMT100 has two 72° and one 60° table BBMMT80 has two 72° and one 60° table BBMMT80 has two 72° and one 60° table BBMMT80 has two 72° and one 60° table BBMMT90 has two 72° and 60° table BBMMT90 has two 72° and 60° table BBMT90 has two 72° and 60° table BBMMT90 has two 72° and 60° tabl													
Includes three tables to dock against the center spine with magnets BBNMT76 has two 48" and one 60" table BBNMT88 has three 60" tables BBNMT10 has two 72" and one 60" table Media sharing equipment must be purchased separately Reference cutout diagram for Extron and FSR grommet locations Tables gang to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Tre% casters come standard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of	BBNM												
the center spine with magnets BBNMT76 has two 48" and one 60" table BBNMT188 has three 60" tables BBNMT100 has two 72" and one 60" table Media sharing equipment must be purchased separately Reference cutout diagram for Extron and FSR grommet locations Tables gang to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come stan- dard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of	Backbone® - Mobile Unit												
the center spine with magnets BBNMT76 has two 48" and one 60" table BBNMT188 has three 60" tables BBNMT100 has two 72" and one 60" table Media sharing equipment must be purchased separately Reference cutout diagram for Extron and FSR grommet locations Tables gang to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come stan- dard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of													
the center spine with magnets BBNMT76 has two 48" and one 60" table BBNMT188 has three 60" tables BBNMT100 has two 72" and one 60" table Media sharing equipment must be purchased separately Reference cutout diagram for Extron and FSR grommet locations Tables gang to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come stan- dard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of	Includes three tables to dock against												
table BBNMT80 has three 60° tables BBNMT100 has two 72° and one 60° table Media sharing equipment must be purchased separately Reference cutout diagram for Extron and FSR grommet locations Tables gang to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come stan- dard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of													
BBNMT88 has three 60° tables BBNMT100 has two 72° and one 60° table Media sharing equipment must be purchased separately Reference cutout diagram for Extron and FSR grommet locations Tables gang to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come stan- dard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of													
BBNMT100 has two 72° and one 60° table Media sharing equipment must be purchased separately Reference cutout diagram for Extron and FSR grommet locations Tables gang to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come standard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of													
Media sharing equipment must be purchased separately Reference cutout diagram for Extron and FSR grommet locations Tables gang to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come standard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of	 BBNMT100 has two 72" and one 60" 												
purchased separately Reference cutout diagram for Extron and FSR grommet locations Tables gang to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come stan- dard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of													
Reference cutout diagram for Extron and FSR grommet locations Tables gang to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come standard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of													
Tables garg to dock Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come standard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of	Reference cutout diagram for Extron												
Perforated end panel will match table base color Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come standard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of													
Center unit has hidden caster for added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come standard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of	 Perforated end panel will match table 												
added mobility Shown with the Enlite® base Tables have a 5% angle on the short ends Enlite® and Trek® casters come standard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of													
Tables have a 5% angle on the short ends Enlite® and Trek® casters come standard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of													
ends Enlite® and Trek® casters come standard 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of	Shown with the Enlite® base Tables have a 50% and be set to a base.												
Enlite® and Trek® casters come standard - 2 locking and 2 non-locking per table Synthesis® comes standard with embedded casters on one end of													
per table Synthesis® comes standard with embedded casters on one end of	Enlite® and Trek® casters come stan-												
Synthesis® comes standard with embedded casters on one end of													
embedded casters on one end of													
each table													
	each table												
31.13.0445			31.13.0445										
RDPT	HRDPT												
Backbone - Master Key for Lock Core	Backbone - Master Key for Lock Core												
Allows course to all Double code	Allows are to all Booking &												
Allows access to all Backbone® panels with a single key	Allows access to all Backbone® namels with a single key.												
parioto with a single key	panois with a single key												

HOW TO ORDER

Indicate the following information on order form:

- 1. Quantity of each item.
- 2. Model number, including options. See "How To Build a Model Number".
- 3. Any special service required.

Note: \bullet The \square indicates that a choice is required.

- \bullet The absence of the \square indicates that no choice is required.
- \bullet Alpha-numeric characters in place of $\hfill\Box$ indicate that no other alternatives are available.

HOW TO BUILD A MODEL NUMBER

- A Select basic model.
- BSelect edge style.

74P - 74P edge

Select table style.

- Enlite style legs - Trek style legs SYN - Synthesis style legs

• Select edge color.

Refer to color addendum at ki.com or KI Fabrics & Finishes binder. Edge color offerings are based on edge style selections.

- Select top laminate. Refer to color addendum at ki.com or KI Fabrics & Finishes binder.
- Select table leg/end panel finish. Refer to color addendum at ki.com or KI Fabrics & Finishes binder.

GSelect dock edge color. Refer to color addendum at ki.com or KI Fabrics & Finishes binder.

- Select dock top laminate. Refer to color addendum at ki.com or KI Fabrics & Finishes binder.
- Select dock base laminate. Refer to color addendum at ki.com or KI Fabrics & Finishes binder.

Select media cutout.

NCO	- No cut-out	
EX4	- Extron 4	
EX5	- Extron 5	Ī
EX6	- Extron 6	
EX7	- Extron 7	
EX8	- Extron 8	Ī
FS1	- FSR (T3)	
FS2	- FSR (T6)	Ī

INFORMATION

Grommet Cutouts by Table Size

Base Length Number of Grommet Cutouts

48" 4 60" 6 72" 6





Approx. Packaged Weight	Delivered Pricing	Enlite Table Bases	Trek Table Bases	Synthesis Table Bases	
353.0#	N/A	\$ 7648	\$ 7752	\$ 7987	
400.0#	N/A	8067	8171	8406	
451.0#	N/A	8818	8922	9157	

1.0#

SPECIAL SERVICES

Special Carton Marking

With specially marked information

N/C

Shipping Shipped k.d. freight prepaid f.o.b. Bonduel, Wisconsin 54107 factory. Freight class #85.

Specifications and prices are subject to change without prior notice.

Backbone® Monitor Support

			I			
			MODEL N	NUMBER		
	MODEL	OVERALL SIZE	Basic Model	Laminate Color	Approx. Packaged Weight	
	Backbone® - Monitor Support For use with Backbone® tables only All laminate construction Must attach to either Mobile or Stationary unit Black grommet cover included Must be ordered separately	38"W x 59"H x 5"D	BBNMS		100.0#	
HRDPT						
HRDPT	Backbone® - Monitor Support - Cafe Height For use with Backbone® tables only All laminate construction Must attach to either Mobile or Stationary unit Black grommet cover included Must be ordered separately Backbone® - Monitor Support-Dual Width For use with Backbone® tables only All laminate construction Must attach to either Mobile or Station-	38"W x 72H" x 5"D	BBNMSC		100.0#	
HRDPT	ary unit Black grommet cover included Must be ordered separately					
	Backbone® - Monitor Support-Cafe Height-Dual Width • For use with Backbone® tables only • All laminate construction • Must attach to either Mobile or Stationary unit • Black grommet cover included • Must be ordered separately	60"W x 72"H x 5"D	BBNMDC		100.0#	
HRDPT						
			A	3	_	

HOW TO ORDER

Indicate the following information on order form:

- Quantity of each item.
 Model number, including options. See
 "How To Build a Model Number".
- 3. Any special service required.

Note: ullet The \square indicates that a choice is required.

- \bullet The absence of the \square indicates that no choice is required.
- · Alpha-numeric characters in place of \square indicate that no other alternatives are available.

HOW TO BUILD A MODEL NUMBER

- A Select basic model.
- BSelect laminate color.

Refer to color addendum at ki.com or KI Fabrics & Finishes binder.





Delivered
Pricing
\$ 2059
\$ 2231
V 2201
\$ 2281
\$ 3076

SPECIAL SERVICES

Special Carton Marking

With specially marked information

N/C

Shipping Shipped k.d. freight prepaid f.o.b. Bonduel, Wisconsin 54107 factory. Freight class #85.

Specifications and prices are subject to change without prior notice.

KI 1330 Bellevue Street P.O. Box 8100 Green Bay, Wisconsin 54308-8100 1-800-424-2432 www.ki.com

KI and Furnishing Knowledge are registered trademarks of Krueger International, Inc.

© 2012 KI All Rights Reserved. Litho in USA. Code KI-11586/KI/PDF/312